

Test Report



Powered by Prym Intimates

| Sample Information | |
|--------------------|-----------------------------------|
| Item Description: | Hook & Eye Fittings/Electroplated |
| Item Category: | Electroplated Hook & Eye Fittings |
| Test Methods: | ISO, AATCC & ASTM |

| Test Method | Requirement | Conformity |
|--|---|------------|
| » COLORFASTNESS TO LAUNDERING: ACCELERATED (AATCC 61 2A) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » COLOURFASTNESS TO PERSPIRATION (ISO 105-E04) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » COLOURFASTNESS TO WATER (ISO 105 E01) | Colour Change : 4.0 Colour Stain : 3.5 | Pass |
| » APPEARANCE AFTER REPEATED LAUNDERING | Visual rating - evaluation after 1x, 5x washed | Pass |
| » FREE NICKEL CONTENT(QUALITATIVE) | Can not be present | Pass |
| » RESISTANCE TO RUST & CORROSION | No corrosion present (Grade 10) | Pass |
| » MANUFACTURING QUALITY (VISUAL) | No sharp points or edges | Pass |



Samples for testing has been selected according to the Random Sampling Technique where each sample has an equal probability of being chosen. There is a possibility that the sample does not represent the population as a whole due to any random variation (Sampling Error). All tests are performed only by certified laboratory technicians.